
INSTALLATION DIMENSIONS LOW PROFILE INSTALL

Enclosure Dimensions




Enclosure width
36"
[914]
Cabinet width at back
35"
[889]


Gap to door edge on both sides
1/8"
[3]

Door width
35 3/4"
[3]

Notes: Except where noted, dimensions are from enclosure to refrigerator.


- (A) If depth is greater than 25 9/16", add shims as needed for anchor bracket. If door protrudes less than 3/4", door will not open properly, and damage to enclosure may occur.
- (B) If decorative trim or other element is applied to front of enclosure, it must be at least 1 3/4" away from enclosure opening.





Notes: Except where noted, dimensions shown are from enclosure to refrigerator.

- (A) Dimension shown based on an enclosure depth of 25 9/16". If the enclosure is shallower, adjust dimension accordingly.
- (B) Recommended minimum side wall clearance of 4 3/4" for 90° door opening.
- (C) Recommended minimum side wall clearance of 18 3/8" for full 115° door opening.



Notes:

- (A) Recommended enclosure height based on installation method:
- Low Profile: 83 1/2" 84"
- (B) Dimensions shown are with rollers in minimum position as shipped. Unit can be raised 1" max.