

3904-51M in leather 824-82

FLEXSTEEL®

© Flexsteel Industries, Inc. | Last Updated 06/23/2023

Rio | 3904

53 51M 51H 51 50M 50H 50	FEATURES
	Flexsteel Spring Unit
•	DualFlex
•	Back Construction Attached
	Seat Construction
•	Attached
•	Seat Cushion(s) High-Density (HC)

Standard

o Optional

PRODUCT DIMENSIONS		OVERALL			SEAT				
	Height	Width	Depth	Height	Width	Depth	Arm Height	Open Depth	Wall Clearance
Swivel Gliding Recliner -53	42"	38"	41"	19"	21"	21"	24"	68"	14"
Power Rocking Recliner -51M	42"	38"	41"	19"	21"	21"	24"	68"	14"
Power Rocking Recliner with Power Headrest -51H	42"	38"	41"	19"	21"	21"	24"	68"	14"
Rocking Recliner -51	42"	38"	41"	19"	21"	21"	24"	68"	4"
Power Recliner -50M	42"	38"	41"	19"	21"	21"	24"	68"	4"
Power Recliner with Power Headrest -50H	42"	38"	41"	19"	21"	21"	24"	68"	4"
Recliner -50	42"	38"	41"	19"	21"	21"	24"	68"	4"

NOTES

Rocking recliner provides soothing movement in the seated position, helping you relax

Power control on the arm effortlessly adjusts the recline, keeping you comfortable $\,$

 $\ensuremath{\mathsf{USB}}$ charging port built into power control keeps devices powered up and ready to use

Divided back cushion cradles your neck, back and lower lumbar for enhanced comfort

Streamlined inset padded armrests have a seamless look and comfortable feel Built to last with our patented Flexsteel DualFlex Spring System™—sturdy steel ribbons attached to flexible coils that offer a wide range of motion and durability High-density cushions consist of a high-resiliency, high-density polyurethane foam core with a soft fiber wrap that ensures comfort as you sit and recline Available in over 50 leather options to suit any décor

Removable back allows for easy lifting and maneuvering through doorways Swivel mechanism allows seamless side-to-side motion

Gliding mechanism provides soothing movement that helps you relax Handle-activated recline system on arm allows you to manually yet efficiently move between sitting and reclining

Footrest easily lowers when you apply pressure in a downward motion Home button returns the headrest and footrest to their original positions with one touch

Power allows you to smoothly recline to any position.

A single USB port is included on each power button control on styles with arms

Lower the footrest by applying pressure to it in a downward motion. Lowering the footrest with the handle can damage the recliner.

The power control allows you to independently adjust the recline and headrest. A separate home button returns the headrest and footrest to their original positions with one touch.

A USB port is included on the power control for powering electronics. Zero draw technology only uses power when the USB port is in use.



Power Recline & Headrest