

CLA-024-105H/F/R-125H/F/R OBLIQUE QUEEN/KING BED

CARACOLE CLASSIC

ASSEMBLY INSTRUCTIONS

TWO (2) PEOPLE AND PHILIP'S SCREWDRIVER REQUIRED

PLEASE UNPACK ALL PARTS AND CHECK AGAINST PARTS LIST ON THIS INSTRUCTION SHEET BEFORE DISCARDING PACKING AND CARTON!!

- 1) Connect the side rails and headboard / footboard by bolt (F).
- 2) Assemble the side rails and headboard / footboard using the curved washer (A), flat washer (B), lock washer (C), and nut (D) tighten with wrench provided (E), as shown in Diagram A.
- 3) Attach the center support rail on the Cleat of headboard & footboard, Using Philips' screw driver to tighten the screw (N) as shown in diagram C.
- 4) Attach the bed slats on the center support rail and cleat of side rails then using Philips' screw driver to tighten the screw (N) as shown in diagram D.
- 5) The bed slats are adjustable and you can move it to another location by Wrench provided (M) as shown in Diagram B.








*** NOTE KEEP THIS SHEET!!! ***




In the unlikely event that you would need a replacement part for your furniture, please contact your local authorized Caracole International dealer. If you need replacement hardware quickly, it could be purchased from your local hardware store.


Part Description	CLA-024-105		CLA-024-125	
	OBLIQUE QUEEN BED	QTY	OBLIQUE KING BED	QTY
Headboard (1)	CLA-024-105-H	1	CLA-024-125-H	1
Footboard (2)	CLA-024-105-F	1	CLA-024-125-F	1
Side Rail (3)	CLA-024-105-R	2	CLA-024-125-R	2
Center Support Rail (4)	CLA-024-105-30290	1	CLA-024-125-30290	2
Slat (5)	CLA-024-105-F-3067	12	CLA-024-125-F-3067	12
RTA Hardware(6)	CLA-024-105-H-30444	1	CLA-024-125-H-30444	1
RTA Hardware(7)	CLA-024-105-R-30443	1	CLA-024-125-R-30443	1
RTA Hardware(8)	CLA-024-105-R-3001	1	CLA-024-125-R-3001	1
Adjustable Cleat on Side Rail	CLA-024-105-R-30442	2	CLA-024-125-R-30442	2
Adjustable Cleat on Headboard	CLA-024-105-H-30441	1	CLA-024-125-H-30441	2
Adjustable Cleat on Footboard	CLA-024-105-H-30441	1	CLA-024-125-H-30441	2
RTA Hardware(9)	CLA-024-105-F-3001	1	CLA-024-125-F-3001	1


RTA Hardware for Center Support Rail of QN Bed (6)		
NO.	Hardware List	Q'ty
G	Bolt(1/4"X38MM)	4
H	Flat Washer(1/4"R8x2MM)	4
I	Lock Washer(1/4"R5x1.5MM)	4


RTA Hardware for Center Support Rail of KG Bed (6)		
NO.	Hardware List	Q'ty
G	Bolt(1/4"X38MM)	8
H	Flat Washer(1/4"R8x2MM)	8
I	Lock Washer(1/4"R5x1.5MM)	8

RTA Hardware For Side rail (8)			
NO.	Hardware List		Q'ty
A		Curved Washer	8
B		Flat Washer(5/16")	8
C		Lock Washer(5/16")	8
D		Nut	8
E		Wrench	1
F		Bolt (8X100MM)	8
M		Wrench	1


RTA Hardware for adjustable side rail cleat (7)			
NO.	Hardware List		Q'ty
G		Bolt(1/4"X38MM)	10
H		Flat Washer(1/4"R8x2MM)	10
I		Lock Washer(1/4"R5x1.5MM)	10

RTA Hardware for bed slats of QN Bed (9)			
N		Screw(4.2x32MM)	62

RTA Hardware for bed slats of KG Bed (9)			
N		Screw(4.2x32MM)	76



QUEEN BED



KING BED

Diagram B




Diagram C




Diagram A




Diagram A

Diagram B

Diagram D

Diagram C

Diagram D




Diagram D






Diagram D



BED MATTRESS DIAGRAM

3 of 3

BEDDING SPECIFICATIONS

CLA-024-125 Dimension of the true mattress opening: 81.5" x 78"

Bed slats: 77.8" x 3" x 0.9"

CLA-024-105 Dimension of the true mattress opening: 81.5" x 62"

Bed slats: 61.9" x 3" x 0.9"

Side rail width: 4"

Height from the floor to bottom of the side rail: 0"

Height from the floor to top of slat: 7.64" (for low setting) or 11.82" (for high setting)

Height from the top of slats to top of side rail: 5.4" (for low setting) or 1.2" (for high setting)

Height from the top of side rail to bottom of headboard pad: 0"

Be sure to adhere to these BEDDING SPECIFICATIONS in order to avoid the possibility of faling or entrapment THESE SPECIFICATIONS MUST BE STRICTLY ADHERE TO!

