



3904-50 in Leather 577-82



3904-50 in Leather 299-70

FLEXSTEEL®

© Flexsteel Industries, Inc. | Last Updated 10/11/2023

53	FEATURES	
51M		
51H		
51		
50M		
50H		
50		
		Flexsteel Spring Unit
●		DualFlex
		Back Construction
●		Attached
		Seat Construction
●		Attached
		Seat Cushion(s)
●		High-Density (HC)

- Standard
- Optional

PRODUCT DIMENSIONS	OVERALL			SEAT			Arm Height	Open Depth	Wall Clearance
	Height	Width	Depth	Height	Width	Depth			
Swivel Gliding Recliner -53	42"	38"	41"	19"	21"	21"	24"	68"	14"
Power Rocking Recliner -51M	42"	38"	41"	19"	21"	21"	24"	68"	14"
Power Rocking Recliner with Power Headrest -51H	42"	38"	41"	19"	21"	21"	24"	68"	14"
Rocking Recliner -51	42"	38"	41"	19"	21"	21"	24"	68"	4"
Power Recliner -50M	42"	38"	41"	19"	21"	21"	24"	68"	4"
Power Recliner with Power Headrest -50H	42"	38"	41"	19"	21"	21"	24"	68"	4"
Recliner -50	42"	38"	41"	19"	21"	21"	24"	68"	4"

NOTES

Handle-activated recline system on arm allows you to manually yet efficiently move between sitting and reclining  
Divided back cushion cradles your neck, back and lower lumbar for enhanced comfort  
Streamlined inset padded armrests have a seamless look and comfortable feel  
Built to last with our patented Flexsteel DualFlex Spring System™—sturdy steel ribbons attached to flexible coils that offer a wide range of motion and durability  
High-density cushions consist of a high-resiliency, high-density polyurethane foam core with a soft fiber wrap that ensures comfort as you sit and recline  
Available in over 50 leather options to suit any décor  
Removable back allows for easy lifting and maneuvering through doorways  
Footrest easily lowers when you apply pressure in a downward motion  
Swivel mechanism allows seamless side-to-side motion  
Gliding mechanism provides soothing movement that helps you relax  
Rocking recliner provides soothing movement in the seated position, helping you relax  
Power control on the arm effortlessly adjusts the recline, keeping you comfortable  
USB charging port built into power control keeps devices powered up and ready to use  
Home button returns the headrest and footrest to their original positions with one touch  
Lower the footrest by applying pressure to it in a downward motion. Lowering the footrest with the handle can damage the recliner.  
Power allows you to smoothly recline to any position.  
A single USB port is included on each power button control on styles with arms.  
The power control allows you to independently adjust the recline and headrest.  
A separate home button returns the headrest and footrest to their original positions with one touch.  
A USB port is included on the power control for powering electronics.  
Zero draw technology only uses power when the USB port is in use.



Power Recline & Headrest