



2804-51M in fabric 123-72



2804-51M in fabric 123-72

2804-51M in fabric 123-72

FLEXSTEEL®

© Flexsteel Industries, Inc. | Last Updated 02/01/2024

Mason | 2804 FABRIC

Mason | 2804

53 51M 51H 51 50M 50H	FEATURES
	Flexsteel Spring Unit
•	DualFlex
	Back Construction
•	Attached
	Seat Construction
•	Attached
	Seat Cushion(s)
•	High-Density (HC)
	Tailoring
0	Arm Covers

lacksquare	Sta	nd	ar	d
------------	-----	----	----	---

o Optional

PRODUCT DIMENSIONS	OVERALL		SEAT						
	Height	Width	Depth	Height	Width	Depth	Arm Height	Open Depth	Wall Clearance
Swivel Gliding Recliner -53	43"	40"	41"	20"	20"	22"	27"	69"	13"
Power Rocking Recliner -51M	43"	40"	41"	20"	20"	22"	27"	69"	13"
Power Rocking Recliner with Power Headrest -51H	43"	40"	41"	20"	20"	22"	27"	69"	13"
Rocking Recliner -51	43"	40"	41"	20"	20"	22"	27"	69"	13"
Power Recliner -50M	43"	40"	41"	20"	20"	22"	27"	69"	5"
Power Recliner with Power Headrest -50H	43"	40"	41"	20"	20"	22"	27"	69"	5"
Recliner -50	43"	40"	41"	20"	20"	22"	27"	69"	5"

NOTES

Rocking motion enhances relaxation

Power control allows you to adjust between sitting and reclining

USB port built into power control for convenient charging

Pad-over armrests enhance comfort and provide additional forearm support

Seat features divided chaise pad for added comfort and refined look

High-divide back cushions have distinctive look and cradle the head, neck and shoulders Biscuit-tufted back cushions the lower back

Built to last with our DualFlex Spring System $^{\text{TM}}$ —sturdy steel ribbons attached to flexible coils that offer a wide range of motion and durability

High-density cushions consist of a high-resiliency, high-density polyurethane foam core with a soft fiber wrap that ensures comfort as you sit and recline with a soft fiber wrap that ensures comfort as you sit and recline

Available in durable, cleanable performance fabrics will withstand everyday use by an active family

Available in over 250 fabrics to suit any décor

Removable back allows for easy lifting and maneuvering through doorways $\,$

Choose whether to glide or recline depending on your activity and mood Handle-activated recline system allows you to manually adjust between sitting and

reclining

Footrest easily lowers when you apply pressure in a downward motion

Power control independently adjusts the headrest and recline for a personalized sit Home button returns the headrest and footrest to their original positions with one touch

Power allows you to smoothly recline to any position.

A single USB port is included on each power button control on styles with arms. Lower the footrest by applying pressure to it in a downward motion. Lowering the footrest with the handle can damage the recliner.

The power control allows you to independently adjust the recline and headrest. A separate home button returns the headrest and footrest to their original positions with one touch.

A USB port is included on the power control for powering electronics. Zero draw technology only uses power when the USB port is in use.



Power Recline & Headrest