



3810-51H in leather 824-74

3810-51H in leather 824-74

$\mathsf{F} \mathsf{L} \mathsf{E} \mathsf{X} \mathsf{S} \mathsf{T} \mathsf{E} \mathsf{E} \mathsf{L}^{\circ}$

© Flexsteel Industries, Inc. | Last Updated 02/01/2024

Arlo | 3810

Arlo | 3810

70"

70"

26"

26"

8"

8"

53 51M		PRODUCT DIMENSIONS	OVERALL			SEAT					
51L 51H 50M 50L 50H 50	FEATURES		Height	Width	Depth	Height	Width	Depth	Arm Height	Open Depth	Wall Clearance
		Swivel Cliding Recliner -53	43"	37"	42"	20"	21"	22"	26"	70"	13"
•	Flexsteel Spring Unit DualFlex	Power Rocking Recliner -51M	43"	37"	42"	20"	21"	22"	26"	70"	13"
•	Back Construction Attached	Power Rocking Recliner with Power Headrest & Lumbar -51L	43"	37"	42"	20"	21"	22"	27"	70"	13"
•	Seat Construction Attached	Power Rocking Recliner with Power Headrest -51H	43"	37"	42"	20"	21"	22"	26"	70"	13"
•	Seat Cushion(s) High-Density (HC)	Rocking Recliner -51	43"	37"	42"	20"	21"	22"	26"	70"	13"
		Power Recliner -50M	43"	37"	42"	20"	21"	22"	26"	70"	8"
• Standard		Power Recliner with Power Headrest & Lumbar -50L	43"	37"	42"	20"	21"	22"	27"	70"	8"

43"

43"

42"

42"

37"

37"

o Optional

NOTES

-50H

-50

Recliner

Power Recliner with Power Headrest

Rocking recliner provides soching movement in the seated position, helping you relax Power control on the arm independently adjusts the headrest and recline for a personalized sit Home button returns the headrest and footrest to their original positions with one touch the provided pad-over track arms enhance comfort and provide additional forearm support Contourdes pad-over track arms enhance comfort and provide additional forearm support Contourdes and virtual to the provide additional forearm support Contourdes pad-over track arms enhance comfort and provide additional forearm support Contourdes pad-over track arms enhance comfort and provide additional forearm support Contourdes pad-over track arms enhance comfort and provide additional forearm support Contourdes pad-over track arms enhance comfort and provide additional forearm support Contourdes pad-over track arms enhance comfort and provide statched to flexible coils that offer a wide range of motion and durability Lingh-density cubinors consistoring adjustem Power the most demanding environments Comfort as you sit and recline Swide mechanism allows seamless side-to-ciside motion Cliating mechanism provides sociting movement that helps you relax Mailable in help upolistery that to helps wirelas Footrest easily lowers when you apply pressure in a downward motion Power control on the arm effortessly adjusts the recline, keeping you confortable The power footrol and helps you to independently adjust the recline and headrest. A separate home buttom returns the headrest and footrest to their original positions with one touch. A Separate home buttom returns the headrest and footrest to their original positions with one touch. A Separate home buttom returns the headrest and footrest to their original positions with one touch. A Separate home buttom returns the headrest and footrest to their original positions with one touch. A power allows you to independently adjust the index. Power allows you to some throm the USB pott is in use. Pro



20"

20"

21"

21"

22"

22"

Power Recline & Headrest



Power Recline, Headrest, & Lumbar

FLEXSTEEL®